



## K5P6C2P1/OCAG1, Aluminum Neutral Bar

By Burndy  
Catalog # [K5P6C2P1/OCAG1](#)



Aluminum Neutral Bar

### General

Catalog Number	K5P6C2P1/OCAG1
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Temperature Rating	194° F
UPC	781810665572
UPC 12 Digit	7818106655722

### Dimensions

Dimension - Height inch	0.62 in
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.26 in
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Size Range	1/0 AWG - 14 AWG
Conductor - Copper Str Size Range	1/0 AWG - 14 AWG

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

### Logistics

Carton Quantity	150
-----------------	-----

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50038330](#)
- [Specifications - BURNDY\\_K5P6C2P1OCAG1\\_Specsheet](#)



A Hubbell brand