

KA29U, AL Set Screw Connector, 1-Hole, #6 AWG Str-250 kcmil, 5/16" Stud, 1 Screw, Al/Cu Rated

By Burndy
Catalog # KA29U



Aluminum Universal Terminal, 1 Hole, 6 AWG (Str)-250 kcmil, 5/16" Stud, 1 Screw, Al/Cu Rated, Tin Plated.

Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy, electro tin-plated to provide low contact resistance

Application

For Aluminum And Copper Conductors

General

Catalog Number	KA29U
Connector Type	Terminal
EU RoHS Indicator	Yes
Installation Torque	275 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370155

Dimensions

Dimension - Bolt Hole Size inch	0.31 in
Dimension - Bolt Size fraction	5/16
Dimension - D inch	0.94 in
Dimension - Height fraction	1.14 in
Dimension - Height inch	1.14 in
Dimension - Height mm	29 mm
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in

Dimension - N inch	0.47 in
Dimension - Pad Width inch	1.02 in
Dimension - Stud Size inch	5/16
Dimension - Width inch	1.00 in
Dimension - Width mm	25 mm

Conductor Related

Conductor - AL Str Size	6;4;3;2;1;1/0;2/0;3/0;4/0;250
Conductor - AL Str Size Range	6-250
Conductor - Copper Str Size	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250
Conductor - Copper Str Size Range	6-250
Conductor - Nominal Diameter	0.184, 0.184, 0.206, 0.232, 0.232, 0.260, 0.260, 0.292, 0.320, 0.328, 0.360, 0.368, 0.390, 0.414, 0.438, 0.464, 0.492, 0.522, 0.528, 0.574, 0.600
Conductor Size	6 AWG-250 KCMIL
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Solid-Size
Number of Conductors	1

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	400
-----------------	-----

Product Assets

[3D Models - KA29U_MODEL-STEP](#)
[3D Models - KA29U_MODEL-PDF](#)

3D Models - KA29U_MODEL-IGES
Catalogs - BURNDY Master Catalog - Section A - Mechanical
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_KAU_Lineart
Sales Drawings - se210997
Specifications - KA29U



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-KA29U-SPEC-EN | REV 10/2024