



# KC26B1NSP, SERVIT POST Mechanical Connector, Cable to Flat

By Burndy  
Catalog # [KC26B1NSP](#)



Mechanical Connector; Cable to Flat; #2 - 2/0 Stranded or #2 - 3/0 Solid; Connector supplied with split lock washer and nut

## General

Catalog Number	KC26B1NSP
Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	480 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810459287
UPC 12 Digit	7818104592877

## Dimensions

Dimension - B Length inch	1.04 in
Dimension - Body Width inch	0.88 in
Dimension - D inch	1.25 in
Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - Nut Width inch	1.04 in
Dimension - P inch	0.44 in

## Conductor Related

Conductor - Copper Solid Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Size Range	2 AWG-3/0 AWG
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	2 AWG-2/0 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Carton Quantity	25
Pallet Quantity	5800

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd055917](#)
- [Specifications - KC26B1NSP](#)