

KLU125, Copper Terminal, Offset Tongue, 1 Hole, 2-1/0 AWG (Str), 1/4" Stud, 1 Screw



By Burndy
Catalog # KLU125

Copper Terminal, Offset Tongue, 1 Hole, 2-1/0 AWG (Str), 1/4" Stud, 1 Screw.

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar

General

Catalog Number	KLU125
Connector Type	Pressure Bar
EU RoHS Indicator	Yes
Hardware Type	3/8 UNF Slotted SetScrew
Installation Torque	50
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	SCRULUG
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810351390

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.61 in
Dimension - Bolt Size fraction	1/4
Dimension - Height mm	0 mm
Dimension - Hole Size inch	0.26 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.98 in

Dimension - N inch	0.42 in
Dimension - Pad Width inch	0.62
Dimension - Screw Size inch	3/8
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	2 AWG-1/0
Conductor Size	2-1/0 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KLU_LineArt](#)
- [Sales Drawings - sd207469-01](#)
- [Specifications - KLU125](#)