



KPA4CTP, Copper Terminal, 1-Hole, #14 AWG Sol-4 AWG Str, 1/4" Stud

By Burndy
Catalog # [KPA4CTP](#)

Copper Terminal, 1 Hole, 14 AWG (Sol)-4 AWG (Str), 1/4" Stud.



Features

- High copper alloy terminal (tin-plated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Terminal Blocks

General

Catalog Number	KPA4CTP
Connector Type	Terminal
EU RoHS Indicator	Yes
Hardware Type	5/16 Dia.Slot Robertson
Installation Torque	45 LBS/in
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Sub Brand	SCRULUG
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810802731

Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - D inch	0.71 in
Dimension - Height fraction	1 in
Dimension - Height inch	1.00 in
Dimension - Height mm	25.4 mm
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.28 in

Dimension - N inch	0.33 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	9/16
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG
Conductor Size	14-4 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

[3D Models - KPA4CTP_MODEL-PDF](#)
[3D Models - KPA4CTP_MODEL-IGES](#)
[3D Models - KPA4CTP_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KPA_Lineart](#)
[Sales Drawings - sd207546-01](#)
[Specifications - KPA4CTP](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-KPA4CTP-SPEC-EN | REV 10/2024