

KPB4CG1, Copper Alloy Clip-on, Lay-in Ground Connector

By Burndy
Catalog # KPB4CG1



Copper Alloy Clip-on/Lay-in Ground Connector, #10 - #4 CU.

Features

- UL467 Listed for Direct Burial in earth or concrete
- UL486 Listed
- Exclusive design accommodates #10-#4 Copper where continuous conductor runs are preferable

Application

For Direct Burial In Earth Or Concrete

General

Catalog Number	KPB4CG1
EU RoHS Indicator	Yes
Installation Torque	45 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw	Steel - Stainless
Plated	N
Plating Type	Tin
Sub Brand	SCRULUG
Type	KPB
UPC	781810100233
UPC 12 Digit	7818101002333

Dimensions

Dimension - B Length inch	0.61 in
Dimension - Height inch	0.95 in
Dimension - Width fraction	1 in
Dimension - Width inch	0.99 in

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • UL 486A-B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • UL 486A-B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	39600

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KPB_LineArt](#)
- [Sales Drawings - SC210191-01_A](#)
- [Specifications - KPB4CG1](#)