

## KS20, Split Bolt Connector, Run/Tap: #8 AWG Str-#4 AWG Sol

By Burndy  
Catalog # [KS20](#)

Copper Split Bolt, Cu: 8 AWG (Str)-4 AWG (Sol) (Run & Tap),Length:1.20.



### Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

### Application

For Direct Burial Applications In Earth Or Concrete, Copper

### General

Catalog Number	KS20
EU RoHS Indicator	Yes
Sub Brand	SERVIT
Type	KS, Compact
UPC	781810012000

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No

Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	100
Pallet Quantity	99000

### Product Assets

[360 Product View - BURN\\_KS20](#)  
[3D Models - KS20\\_MODEL-PDF](#)  
[3D Models - KS20\\_MODEL-IGES](#)  
[3D Models - KS20\\_MODEL-STEP](#)  
[3D Product View - BURN\\_KS20](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SD..078561-01](#)  
[Sell Sheets - SERVIT® Split-bolt Connectors](#)  
[Specifications - KS20](#)