

## KS25, Split Bolt Connector, Run/Tap: #4 AWG-1/0 AWG Str

By Burndy  
Catalog # KS25



Copper Split Bolt, Cu: 4 AWG-1/0 AWG (Str) (Run & Tap).

### Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

### Application

For Direct Burial Applications In Earth Or Concrete, Copper

### General

Catalog Number	KS25
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque	385 in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810013106
UPC 12 Digit	7818100131066

### Dimensions

Dimension - B Length fraction	83/100 in
Dimension - B Length inch	.83 in
Dimension - Cross Flats inch	0.94 in
Dimension - L Length Overall mm	45 mm
Dimension - Length Overall inch	1.77
Dimension - Width fraction	73/100 in
Dimension - Width inch	0.73 in
Dimension - Width mm	19 mm
Width	0.73 in

### Conductor Related

Conductor - Copper Solid Run	2/0 AWG
Conductor - Copper Solid Run Range	4 AWG-1/0

Conductor - Copper Solid Tap	2/0 AWG
Conductor - Copper Solid Tap Range	14 AWG-1/0
Conductor - Copper Str Run	4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Run Range	4 STR - 1/0 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Tap Range	4 STR - 1/0 STR
Conductor - CopperWeld Solid Run	2/0
Conductor - CopperWeld Solid Run Range	2/0
Conductor - CopperWeld Solid Tap	2/0
Conductor - CopperWeld Solid Tap Range	2/0
Conductor - CopperWeld Str Run	4 D AWG;4 N AWG;4 P AWG;3 A AWG;3 J AWG;3 K AWG;3 N AWG;3 P AWG;2 A AWG
Conductor - CopperWeld Str Run Range	4 D AWG-2 A AWG
Conductor - CopperWeld Str Tap	5 D AWG;5 P AWG;4 A AWG;4 D AWG;4 N AWG;4 P AWG;3 A AWG;3 J AWG;3 K AWG;3 N AWG;3 P AWG;2 A AWG
Conductor - CopperWeld Str Tap Range	5 D AWG-2 A AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• CU Weld C Solid-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Solid-Tap</li> <li>• CU Weld C Str-Tap</li> <li>• CU C Solid-Tap</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	Yes

**Logistics**

Carton Quantity	50
Pallet Quantity	11600

**Product Assets**

- 3D Models - KS25\_MODEL-STEP
- 3D Models - KS25\_MODEL-PDF
- 3D Models - KS25\_MODEL-IGES
- Catalogs - BURNDY Master Catalog - Section A - Mechanical
- Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Customer Notices - Prop 65 Notice
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Product Cross Section Image(s) - BUR\_KS\_Lineart\_BW
- Sales Drawings - SD..078561-01
- Sell Sheets - SERVIT® Split-bolt Connectors
- Specifications - KS25



A Hubbell brand