

KS26, Split Bolt Connector, Run/Tap: #2 AWG-2/0 AWG Str

By Burndy
Catalog # [KS26](#)



Copper Split Bolt, Cu: 2 AWG-2/0 AWG (Str) (Run & Tap).

Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Application

For Direct Burial Applications In Earth Or Concrete, Copper

General

Catalog Number	KS26
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque	385 in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810013281
UPC 12 Digit	7818100132811

Dimensions

Dimension - B Length fraction	9/10 in
Dimension - B Length inch	.90 in
Dimension - Cross Flats inch	1.05 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94
Dimension - Width fraction	41/50 in
Dimension - Width inch	0.82 in
Dimension - Width mm	21 mm
Width	0.82 in

Conductor Related

Conductor - Copper Solid Run	3/0 AWG
Conductor - Copper Solid Run Range	2 AWG-2/0 AWG

Conductor - Copper Solid Tap	3/0 AWG
Conductor - Copper Solid Tap Range	14 AWG-2/0 AWG
Conductor - Copper Str Run	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	2 STR - 2/0 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	2 STR - 2/0 STR
Conductor - CopperWeld Solid Run	3/0
Conductor - CopperWeld Solid Run Range	3/0
Conductor - CopperWeld Solid Tap	3/0
Conductor - CopperWeld Solid Tap Range	3/0
Conductor - CopperWeld Str Run	7 #7
Conductor - CopperWeld Str Run Range	7 #7
Conductor - CopperWeld Str Tap	7 #7
Conductor - CopperWeld Str Tap Range	7 #7
Conductor - Rebar Size	3
Conductor - Rebar Size Range	3
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> UL 486A UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> UL 486A UL486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	25
Pallet Quantity	8700

Product Assets

[3D Models - KS26_MODEL-STEP](#)
[3D Models - KS26_MODEL-IGES](#)
[3D Models - KS26_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KS_Lineart_BW](#)
[Sales Drawings - SD..078561-01](#)
[Sell Sheets - SERVIT® Split-bolt Connectors](#)
[Specifications - KS26](#)



A Hubbell brand