

KS34, Split Bolt Connector, Run/Tap: 2/0 AWG Str-500 kcmil

By Burndy
Catalog # [KS34](#)



Copper Split Bolt, Cu: 2/0 AWG (Str)-500 kcmil (Run & Tap).

Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Application

For Direct Burial Cables

General

Catalog Number	KS34
EU RoHS Indicator	Yes
Material	Copper
Sub Brand	SERVIT
Type	KS
UPC	781810014509

Conductor Related

Conductor Type	<ul style="list-style-type: none">• CU C Solid-Run• CU C Str-Run• CU Weld C Solid-Run• CU Weld C Str-Run
----------------	---

- CU C Str-Tap
- CU Weld C Solid-Tap
- CU Weld C Str-Tap
- CU C Solid-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Product Assets

- [3D Models - KS34_MODEL-PDF](#)
- [3D Models - KS34_MODEL-IGES](#)
- [3D Models - KS34_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD..078561-01](#)
- [Sell Sheets - SERVIT® Split-bolt Connectors](#)
- [Specifications - KS34](#)