

KS44, Split Bolt Connector, Run/Tap: 300-1000 kcmil

By Burndy
Catalog # [KS44](#)



Copper Split Bolt, Cu: 300-1000 kcmil (Run & Tap).

Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Application

For Direct Burial Cables

General

Catalog Number	KS44
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque	1100 in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS
UPC	781810015001
UPC 12 Digit	7818100150011

Dimensions

Dimension - B Length inch	2.10 in
Dimension - Cross Flats inch	2.56 in
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.9
Dimension - Width inch	2.19 in
Dimension - Width mm	56 mm
Width	2.19 in

Conductor Related

Conductor - Copper Str Run	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
----------------------------	--

Conductor - Copper Str Run Range	300 KCMIL - 1000 KCMIL
Conductor - Copper Str Tap	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Tap Range	300 KCMIL - 1000 KCMIL
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Product Assets

[3D Models - KS44_MODEL-STEP](#)
[3D Models - KS44_MODEL-PDF](#)
[3D Models - KS44_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KS_Lineart_BW](#)
[Sales Drawings - SD..078561-01](#)



A Hubbell brand