

KS90, Split Bolt Connector, Run/Tap: #12-10 AWG Str

By Burndy
Catalog # KS90



Copper Split Bolt, Cu: 12-10 AWG (Str) (Run & Tap).

Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Application

For Direct Burial Cables

General

Catalog Number	KS90
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque	80 in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS
UPC	781810015254
UPC 12 Digit	7818100152544

Dimensions

Dimension - B Length fraction	9/20 in
Dimension - B Length inch	.45 in
Dimension - Cross Flats inch	.50 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.85
Dimension - Width fraction	19/50 in
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm
Width	0.38 in

Conductor Related

Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Run Range	10 AWG-12 AWG

Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Solid Tap Range	16 AWG-10 AWG
Conductor - Copper Str Run	12 AWG;10 AWG
Conductor - Copper Str Run Range	12 STR. 10 STR.
Conductor - Copper Str Tap	16 AWG;14 AWG;12 AWG;10 AWG
Conductor - Copper Str Tap Range	16 STR.
Conductor - CopperWeld Solid Run	#10
Conductor - CopperWeld Solid Run Range	#10
Conductor - CopperWeld Solid Tap	#10
Conductor - CopperWeld Solid Tap Range	#10
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
-----------------	-----

Pallet Quantity

99000

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_KS_Lineart_BW

Sales Drawings - SD..078561-01

Sell Sheets - SERVIT® Split-bolt Connectors

Specifications - KS90

Product Assets

3D Models - KS90_MODEL-STEP

3D Models - KS90_MODEL-PDF

3D Models - KS90_MODEL-IGES

Catalogs - BURNDY Master Catalog - Section A - Mechanical



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-KS90-SPEC-EN | REV 10/2024