

KSU23, Split Bolt Connector with Spacer, Tin Plated

By Burndy
Catalog # KSU23



Tin-plated, high strength copper alloy SERVIT with spacer. Spacer separates dissimilar conductors and provides long contact length that prevents high pressure point contacts between run and tap conductors, 1.48 IN L.

Features

- Tin-plated, high strength copper alloy with spacer
- Spacer separates dissimilar conductors and provides long contact length preventing high pressure point contacts between run and tap conductors

Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC, 5005, And Steel

General

Catalog Number	KSU23
EU RoHS Indicator	Yes
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNIVERSAL SERVIT
Trade Name	SERVIT®
Type	KSU, Universal
UPC	781810036006

Dimensions

Dimension - Length Overall	1.56
inch	
Width	0.59 in

Conductor Related

Conductor - ACSR Str Run Range	3 AWG - 2 AWG
Conductor - ACSR Str Tap Range	6 AWG - 2 AWG
Conductor - AL Str Run Range	8 AWG - 2 AWG
Conductor - AL Str Tap Range	8 AWG - 2 AWG
Conductor - Copper Str Run Range	8 AWG - 2 AWG
Conductor - Copper Str Tap Range	8 AWG - 2 AWG

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	17400

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD..041343-01](#)
- [Specifications - KSU23](#)