

Full Cycle Ratchet Hand Crimper, #26 AWG - #8 AWG, N Die

By Burndy
Catalog # [M8ND](#)



Full Cycle Ratchet Hand Crimper, #26-#8 AWG.

Features

- Fully protected ratchet mechanism
- Reinforced heavy duty back
- Long handles provide greater mechanical advantages
- Uses all standard BURNDY N-dies
- Easy groove identification with color-coded dies

Application

Crimping

General

Application - For Use On	#26-8 AWG Terminals and Splices
Catalog Number	M8ND
Die Type	N Die
EU RoHS Indicator	Yes
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810029817
UPC 12 Digit	7818100298177

Dimensions

Dimension - Length Overall	10.75 in
inch	
Dimension - Thread Size	-
Dimension - Width inch	1-3/4 in
Length	10.75 in

Certifications And Compliance

Standards - RoHS Compliance	EX
Status	

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_082_0TOF_M8ND_lineart](#)
[Sales Drawings - sd030323-01](#)
[Specifications - M8ND](#)