



Manual Cable Cutter, up to 1000 kcmil Copper and Aluminum

By Burndy
Catalog # [MCC1000](#)

Manual Cable Cutter, up to 1000 kcmil CU/AL.



Application

Cutting

General

Application - For Use On	Aluminum, Copper Cable
Catalog Number	MCC1000
EU RoHS Indicator	Yes
Tool Type	Manual Cable Cutter
Type	Cutter
UPC	781810174869
UPC 12 Digit	7818101748699

Dimensions

Cable Insulation Diameter Maximum	1.9 in
Length	32 in
Weight	9 lb
Width	6 in

Conductor Related

Crimping Ranges	Cutting Capacity : Copper upto 1000 kcmil; Aluminum: upto 1000 kcmil
-----------------	--

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_MCC_CUTTER_LineArt](#)
- [Sales Drawings - SE211277-01_A](#)
- [Specifications - MCC1000](#)