



Manual Cable Cutter, up to 600 kcmil Copper and Aluminum

By Burndy
Catalog # [MCC600](#)

Manual Cable Cutter, up to 600 kcmil CU/AL.



Application

Cutting

General

Application - For Use On	Aluminum, Copper Cable
Catalog Number	MCC600
Tool Type	Manual Cable Cutter
Type	Cutter
UPC	781810566114
UPC 12 Digit	7818105661144

Dimensions

Cable Insulation Diameter Maximum	1.31 in
Length	21 in
Weight	3.5 lb
Width	5 in

Conductor Related

Crimping Ranges

Cutting Capacity : Copper upto 600 kcmil; Aluminum: upto 600 kcmil

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Package Contents Tool only

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - Cutters](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50009950-01_B](#)
- [Specifications - MCC600](#)