



HYTOOL™ Hand-Operated Crimper, Installs #14 - 4/0 AWG, Permanent BG (5/8) and D3 grooves

By Burndy
Catalog # [MD6](#)



Crimper, Installs #14-4/0 AWG, BG & D3 Grooves.

Application

- Crimping

General

| | |
|--------------------------|---|
| Application - For Use On | Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors |
| Catalog Number | MD6 |
| Crimp Force Capacity | 4.5 ton |
| Die Type | W Die and X Die |
| EU RoHS Indicator | Yes |
| Tool Type | Hand Operated Crimper |
| Trade Name | HYTOOL™ |
| UPC | 781810446003 |
| UPC 12 Digit | 7818104460033 |

Dimensions

| | |
|------------|------------------------------|
| Dimensions | 25.38 in x 7.04 in x 2.00 in |
| Height | 2 in |
| Length | 25.38 in |
| Weight | 6.25 lb |

Width 7.04 in

Conductor Related

Crimping Ranges Copper: 10 sol. - 500 Kcmil;
Copper Flex: #8 to 350 kcmil

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Package Contents Tool only

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - BUR_464750_MD6_MD66_MD637_MD638](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_MD6_Lineart](#)
[Sales Drawings - 2240](#)
[Specifications - MD6](#)