

HYTOOL™ Hand-Operated Crimper, Installs #14 - 4/0 AWG, Permanent O and D3 grooves

By Burndy
Catalog # [MD68](#)



Crimper, Installs #14-4/0 AWG, O & D3 Grooves.

Application

- Crimping

General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Catalog Number	MD68
Crimp Force Capacity	4.5 ton
Die Type	W Die and X Die
EU RoHS Indicator	Yes
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
UPC	781810446553
UPC 12 Digit	7818104465533

Dimensions

Dimensions	25.38 in x 7.04 in x 2.00 in
Height	2 in
Length	25.38 in
Weight	6 lb

Width 7.04 in

Conductor Related

Crimping Ranges Copper: 10 sol. - 500 Kcmil;
Copper Flex: #8 to 350 kcmil

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Package Contents Tool only

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_MD68_LA](#)
[Sales Drawings - SE068728](#)
[Specifications - MD68](#)