



# HYTOOL™ Hand-Operated Crimper, Polymer Handles, #14 - 4/0 AWG, Permanent BG (5/8) and D3 grooves

By Burndy  
Catalog # [MD7](#)



Crimper, Polymer Handles, #14-4/0 AWG, BG & D3 Grooves.

## Application

Crimping

## General

Application - For Use On Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors

Catalog Number MD7  
Crimp Force Capacity 4.5 ton  
Die Type W and X Die  
EU RoHS Indicator Yes  
Tool Type Hand Operated Crimper  
Trade Name HYTOOL™  
UPC 781810010914  
UPC 12 Digit 7818100109144

## Dimensions

Dimensions 25.00 in x 4.50 in x 2.00 in  
Height 2 in  
Length 25 in  
Weight 7 lb  
Width 4.5 in

## Conductor Related

Crimping Ranges Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol.

to 4/0 ACSR; Stirrups: #6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Carton Quantity 1  
Package Contents Tool only

## Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_082\\_0T2F\\_MD7\\_lineart2](#)  
[Sales Drawings - se207642-01](#)  
[Specifications - MD7](#)