



# Ergonomic Full Cycle Ratchet Crimper, For use on #22-#10 Nylon and Vinyl Insulated Terminals and Splices



By Burndy  
Catalog # [MRE1022NV](#)

Full Cycle Ratchet Crimper, #22-#10 Nylon and Vinyl Insulated.

## Application

- Crimping

## General

Application - For Use On	Nylon and Vinyl Insulated Terminals and Splices
Catalog Number	MRE1022NV
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810512999
UPC 12 Digit	7818105129999

## Dimensions

Dimensions	10.68 in x 3.00 in x 0.63 in
Height	0.63 in
Length	10.68 in
Weight	1.3 lb
Width	3 in

## Conductor Related

Crimping Ranges Copper: #22 AWG - #10 AWG

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Package Contents Tool only

## Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - BUR\\_30009440\\_SOMI\\_MRE10-22B and MRE10-22NV](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_MRE1022\\_lineart](#)  
[Sales Drawings - 30013557](#)  
[Specifications - MRE1022NV](#)