



# Dieless Mechanical Crimper, Fully Covered, #8 Str - 250 kcmil Copper Code, #8 Str - 4/0 Str Aluminum Code, 30 Navy - 250 Navy Copper Navy Cable

By Burndy  
Catalog # [MY293CF](#)



Dieless Crimper, Fully Covered.

## Application

Crimping

## General

Application - For Use On	#8-250 kcmil CU Code, 30 Navy-250 Navy CU Navy Cable, #8-4/0 AL Code
Catalog Number	MY293CF
Die Type	Dieless
Tool Type	Mechanical Dieless Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810034170
UPC 12 Digit	7818100341700

## Dimensions

Dimensions	22.65 in x 4.86 in x 1.12 in
Height	1.12 in
Length	22.65 in
Weight	8 lb
Width	4.86 in

## Conductor Related

Crimping Ranges #8 Str. - 250 kcmil, 30 Navy - 250 Navy, #8 Str. - 4/0 Str

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Package Contents Tool only

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_MY\\_LineArt](#)
- [Sales Drawings - sd026316-01](#)
- [Specifications - MY293CF](#)