



4.5-Ton OEM Pneumatic Bench Press, #8 AWG - 4/0 AWG

By Burndy
Catalog # [OEM840NCP](#)

4.5T OEM Pneumatic Bench Press.



Application

Crimping

General

Application - For Use On	Use with UM, U and W Dies
Catalog Number	OEM840NCP
Die Type	UM Die
Tool Type	Pneumatic Press
Type	Crimper
UPC	781810660379

Dimensions

Dimensions	18.56 in x 10.26 in x 22.01 in
Height	22.01 in
Length	18.56 in
Weight	61 lb
Width	10.26 in

Conductor Related

Crimping Ranges Installs #8 - 4/0 AWG

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Package Contents Bench Press, foot switch
(accessories sold separately)

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50024706](#)
[SDS - Non-Detergent Motor Oil SDS \(2013-06\)](#)
[Specifications - OEM840NCP](#)