

# PATRIOT® 15-Ton Latch Head Battery Actuated Crimper, Hydraulic Self-Contained, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case



By Burndy  
Catalog # PAT46LWLI

PAT46 15T Latch Head Battery Crimper, 3Ah Li-ion, AC, Hard Case.

## Application

- Crimping

## General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT46LWLI
Container Type	Hard Case
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
EU RoHS Indicator	Under Review
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	781810654675
UPC 12 Digit	7818106546755

## Dimensions

Dimension - Height mm	349.3 mm
Dimensions	18.59 in x 3.26 in x 13.93 in
Height	13.93 in
Jaw Width	2.00 in
Length	18.59 in

Weight	15.5 lb
Width	3.26 in

## Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

## Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter
-----------------	--

## Certifications And Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

## Logistics

Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case
------------------	---

## Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_PAT46LW\\_LineArt](#)  
[Sales Drawings - 50002858](#)  
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)  
[Specifications - PAT46LWLI](#)