



PATRIOT® 15-Ton C-Head Battery Actuated Crimper, Hydraulic Self-Contained, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # [PAT46LWSLI](#)



PAT46 15T C-Head Battery Crimper, 3Ah Li-ion, AC, Hard Case.

Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT46LWSLI
Container Type	Hard Case
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
EU RoHS Indicator	Under Review
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	781810671535
UPC 12 Digit	7818106715355

Dimensions

Dimensions	18.44 in x 3.26 in x 12.88 in
Height	12.88 in
Jaw Width	2.00 in
Length	18.44 in
Weight	17.65 lb
Width	3.26 in

Electrical Ratings

Operating Voltage 18 VDC

Conductor Related

Crimping Ranges Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter

Certifications And Compliance

Standards - RoHS Compliance UI Status

Logistics

Minimum Pack Quantity 1
Package Contents Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50024801](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)
[Specifications - PAT46LWSLI](#)