



PATRIOT® 4-POINT® 6-Ton Dieless C-Head Battery Actuated Crimper, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # [PAT4PC834LI](#)

PAT4PC834 4-POINT® 6T Dieless C-Head Battery Crimper, 3Ah Li-ion, AC, Hard Case.



Features

- Dieless System with range taking capabilities
- 360° head rotation
- 1.06" Jaw opening
- Overmolded handle for comfort and improved grip
- Ergonomically balanced

Application

Crimping

General

Application - For Use On	Copper, Aluminum Terminals and Splices, HYPLUG™
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Container Type	Hard Case
Crimp Force Capacity	6 ton
Die Type	Dieless
EU RoHS Indicator	Yes
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT® 4-POINT®
Type	Crimper
UPC	781810505441
UPC 12 Digit	7818105054411

Dimensions

Dimensions	15.60 in x 3.20 in x 14.10 in
Height	14.10 in
Length	15.60 in
Weight	12.50 lb
Width	3.20 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #8 AWG - 1000 kcmil; Copper Flex: #8 AWG - 777.7 kcmil; Aluminum: #8 AWG - 750 kcmil
-----------------	---

Certifications and Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case
------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 30003020](#)
[SDS - Burndy BAT18VLI SDS Sheet \(2022-02\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-PAT4PC834LI-SPEC-EN | REV 1/2024