



**Hydraulic Hose, 10', 3/16" dia non-cond, Stackable couplers (male/female), Orange, Min burst pressure 40,000 psi, Nom working pressure 10,000 psi**

By Burndy  
Catalog # [PT2990010](#)

Hydraulic Hose, 10' x 3/16" dia N/C, Stackable (M/F), Orange, 10K psi.

**Application**

Accessory, Hose

**General**

Catalog Number	PT2990010
EU RoHS Indicator	Yes
Type	Hydraulic Accessories
UPC	781810625668

**Certifications And Compliance**

Standards - RoHS Compliance    EX  
Status

**Logistics**

Package Contents                      Hose, Couplers

**Product Assets**

- [Catalogs - Conductor Support Equipment](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE088658-01\\_A](#)
- [Specifications - PT2990010](#)