



Hydraulic Hose, 10', 3/16" dia non-cond, Stackable couplers (male/female), Orange, Min burst pressure 40,000 psi, Nom working pressure 10,000 psi

By Burndy
Catalog # [PT2990010](#)



Hydraulic Hose, 10' x 3/16" dia N/C, Stackable (M/F), Orange, 10K psi.

Application

Accessory, Hose

General

Catalog Number	PT2990010
EU RoHS Indicator	Yes
Type	Hydraulic Accessories
UPC	781810625668

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Package Contents Hose, Couplers

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE088658-01_A](#)
[Specifications - PT2990010](#)