



## PTV10, Vinyl Pin Terminal For 12 - 10 AWG

By Burndy  
Catalog # PTV10

Cu Pin Terminal, 10-12 AWG, 0.97" L, 0.11" W, Molded Vinyl Insul, Tin Plated, Yellow(Insul Color)



### Features

- Vinyl Insulation
- Color-coded barrels
- Provides an easy and effective way to terminate stranded wire into European/Metric-style terminal blocks

### General

Catalog Number	PTV10
Connector Type	Pin Terminal
EU RoHS Indicator	Contact Manufacturer
UPC	781810530627
UPC 12 Digit	7818105306277

### Dimensions

Dimension - B Length inch	0.27 in
Dimension - Length Overall inch	0.97 in
Dimension - Pad Size inch	0.50 in
Dimension - Pad Width inch	0.11 in
Dimension - Strip Length inch	5/16 in

### Conductor Related

Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Product Assets

- [3D Models - PTV10\\_MODEL-IGES](#)
- [3D Models - PTV10\\_MODEL-PDF](#)
- [3D Models - PTV10\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30014756](#)