



PTV18, Vinyl Pin Terminal For 22 - 18 AWG

By Burndy
Catalog # PTV18

Cu Pin Terminal, 18-22 AWG, 0.80" L, 0.07" W, Molded Vinyl Insul, Tin Plated, Red(Insul Color)



Features

- Vinyl Insulation
- Color-coded barrels
- Provides an easy and effective way to terminate stranded wire into European/Metric-style terminal blocks

General

Catalog Number	PTV18
Connector Type	Pin Terminal
UPC	781810530603
UPC 12 Digit	7818105306033

Dimensions

Dimension - B Length inch	0.19 in
Dimension - Length Overall inch	0.8 in
Dimension - Pad Size inch	0.41 in
Dimension - Pad Width inch	0.07 in
Dimension - Strip Length inch	5/16 in

Conductor Related

Conductor - Copper Solid Size Range	22 AWG-18 AWG
Conductor - Copper Str Size Range	22 AWG-18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

Product Assets

- [3D Models - PTV18_MODEL-PDF](#)
- [3D Models - PTV18_MODEL-IGES](#)
- [3D Models - PTV18_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30014756](#)
- [Specifications - PTV18](#)