

## QP14M25X03D, Vinyl Male Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy  
Catalog # [QP14M25X03D](#)



Brass Male Quick Disconnect, 14-16 AWG, Vinyl Insulated, Install with MRE1022NV, Y1022, Y10D.

### Features

- Butted seam
- Funnel entry barrel opening for quick and easy wire insertion
- Mates with dimpled female socket detent for a firm grip

### Application

For quickly connecting or disconnecting a terminal

### General

Catalog Number	QP14M25X03D
Connector Type	Male Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293485
UPC 12 Digit	7818102934855

### Dimensions

Dimension - Length Overall inch	0.84 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor Range	#14 AWG to #16 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1200
Pallet Quantity	99999

### Product Assets

[3D Models - QP14M25X03D\\_MODEL-STEP](#)  
[3D Models - QP14M25X03D\\_MODEL-IGES](#)  
[3D Models - QP14M25X03D\\_MODEL-PDF](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_KPFQPM\\_LineArt](#)  
[Sales Drawings - 50094206](#)  
[Specifications - QP14M25X03D](#)