



QP18F25X03D, Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy

Catalog # [QP18F25X03D](#)



Brass Female Quick Disconnect, 18-22 AWG, Vinyl Insulated, Tin Plated.

Application

For quickly connecting or disconnecting a terminal

General

Catalog Number	QP18F25X03D
Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293195
UPC 12 Digit	7818102931955

Dimensions

Dimension - Length Overall inch	0.87 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#16 AWG to #22 AWG
-----------------	--------------------

Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1200
Pallet Quantity	99999

Product Assets

- [3D Models - QP18F25X03D_MODEL-STEP](#)
- [3D Models - QP18F25X03D_MODEL-IGES](#)
- [3D Models - QP18F25X03D_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KPFQPF_LineArt](#)
- [Sales Drawings - 50094207](#)
- [Specifications - QP18F25X03D](#)