



QPX3434Y, Mechanical Parallel Clamp for Cu/AL, 250-500 kcmil Run; 250-500 kcmil Tap

By Burndy
Catalog # [QPX3434Y](#)



VERSITAP™ Mechanical Parallel Clamp for Copper and Aluminum; Run: 250 - 500 kcmil; Tap: 250 - 500 kcmil

General

Catalog Number	QPX3434Y
Connector Type	Universal Clamp
Installation Torque	375 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	VERSITAP™
UPC	781810343302
UPC 12 Digit	7818103433022

Dimensions

Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.88
Dimension - L Length Overall mm	64 mm
Dimension - Length Overall inch	2.50 in
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	2.54
Dimension - Width mm	65 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Run Range	250 kcmil-500 kcmil
Conductor - AL Str Tap	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Tap Range	250 kcmil-500 kcmil
Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Tap	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Tap Range	250 kcmil-500 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) -](#)

[BUR_QPX_PARA_CLAMP_LineArt](#)

[Sales Drawings - sd..026550](#)

[Specifications - BURNDY_QPX3434Y_Specsheet](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-QPX3434Y-SPEC-EN | REV 8/2024