



Remote Hydraulic Cutter, 10000 psi, Cuts up to 1.29" Copper and Aluminum, 1113 kcmil ACSR

By Burndy
Catalog # [RHCC129ACSR](#)

Remote Hydraulic Cutter, 10000 psi, Cuts up to 1.29" CU/AL, 1113 kcmil ACSR.



Application

Cutting

General

Application - For Use On	ACSR, Aluminum, Copper Cable; Ground Rod; Rebar; Soft Steel Bolts; Standard Guy; EHS Guy Strand
Catalog Number	RHCC129ACSR
EU RoHS Indicator	Yes
Tool Type	Remote Hydraulic Cutter
Type	Cutter
UPC	781810372357
UPC 12 Digit	7818103723577

Dimensions

Dimensions	11.41 in x 3.65 in x 2.33 in
Height	2.33 in
Length	11.41 in
Weight	6.21 lb
Width	3.65 in

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity	1
Package Contents	Tool, Canvas Carry Bag
Pallet Quantity	168

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_RHCC129ACSR_lineart](#)
- [Sales Drawings - 10046861](#)
- [Specifications - RHCC129ACSR](#)