



RK1942, Convenience packaging of WIREMIKE™ (with inch markings), sold in multiples of 10 only, 4.38 in L, 1.94 in W



By Burndy
Catalog # RK1942

Wire Mike, #6 - 336.4 (26/7) str. ACSR #18 str. - 2,000 kcmil #20 sol. - 4/0 sol., 4.38 in L, 1.52 in W.

Application

- Grounding

General

Catalog Number	RK1942
EU RoHS Indicator	Yes
Material	Vinyl, Textured
Sub Brand	ACCESSORY
Tool Type	WIRE MIKE COVER
Type	WIREMIKE
UPC	781810024409
UPC 12 Digit	7818100244099

Dimensions

Length	4.38 in
Width	1.94 in

Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Carton Quantity	10
Pallet Quantity	4640

Product Assets

- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_RK1942_LineArt](#)
- [Sales Drawings - 50015434](#)
- [Specifications - RK1942](#)