

# T1010F, Uninsulated Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # T1010F



Copper Compression Terminal, Fork Tongue, 12-10 AWG, #8-#10 Stud, Long Barrel, Tin Plated.

## Application

For Control Wiring And Other Standard Duty Applications

## General

Catalog Number	T1010F
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	T-F
UPC	781810722107
UPC 12 Digit	7818107221077

## Dimensions

Cable Insulation Diameter Maximum	0.12 in
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Diameter Max Size inch	0.12 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.87 in
Dimension - Pad Width inch	0.41 in

Dimension - Strip Length inch	11/32
Dimension - Stud Size inch	#8;#9;#10
Dimension - Z (inch)	0.32 in

## Conductor Related

Conductor - Copper Str Size	14 AWG;10 AWG (Str.);12 AWG (Sol.);10 AWG
Conductor - Copper Str Size Range	14 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	600
Pallet Quantity	99999

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_tfla](#)
- [Sales Drawings - 50094170](#)
- [Specifications - T1010F](#)