


T1414, Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # T1414



Copper Compression Terminal, Ring Tongue, 20-14 AWG, 1/4" Stud, Long Barrel, Tin Plated.

Features

Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For Control Wiring And Other Standard Duty Applications

General

Catalog Number	T1414
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810722480
UPC 12 Digit	7818107224800

Dimensions

Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Bolt Size fraction	1/4
Dimension - Diameter Max Size inch	0.08 in
Dimension - Hole Size fraction	17/63
Dimension - Hole Size inch	0.27 in
Dimension - L Length Overall mm	24
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.45 in

Dimension - Strip Length inch	9/32
Dimension - Stud Size inch	1/4 in
Dimension - Z (inch)	0.47 in

Conductor Related

Conductor Range	#20 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1200
Pallet Quantity	99999

Product Assets

- [3D Models - T1414_MODEL-PDF](#)
- [3D Models - T1414_MODEL-STEP](#)
- [3D Models - T1414_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_K6FT_LineArt](#)
- [Sales Drawings - 50094154](#)
- [Specifications - T1414](#)