



# TMHG42, Stainless Steel Hardware Kit for I-Beam Connector (not included)

By Burndy  
Catalog # [TMHG42](#)



Stainless Steel Hardware Kit For I-Beam Connector, 1/2" Screw, 0.42" Max. Terminal Pad Thickness.

## Application

An irreversible compression ground connection which allows attachment to a structural steel standard (angled) or wide flange (para llel) beam.

## General

Catalog Number	TMHG42
Connector Type	Hardware
EU RoHS Indicator	Yes
Material	STAINLESS STEEL
Sub Brand	INSULUG
Type	Compression Ground Connector
UPC	781810035054
UPC 12 Digit	7818100350544

## Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - Thread Size	1/2 - 13

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"><li>UL 486A-B</li><li>IEEE 837</li></ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"><li>UL 486A-B</li><li>IEEE 837</li></ul>
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	12
Pallet Quantity	5568

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_TMH\\_LineArt](#)
- [Sales Drawings - 50048710](#)
- [Specifications - TMHG42](#)