

TN1014, Nylon Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [TN1014](#)

Copper Terminal, Ring Tongue, 12-10 AWG, #12,1/4" Stud, 600 Volts Max., Nylon Insulated, Funnel Entry, Tin Plated.

Features

- Deep inner barrel serrations and smooth funnel entry provide excellent conductivity and pullout strength values with easy wire insertion
- Color-coded and clearly marked for quick easy wire size identification

Application

For Heavy Duty Industrial, Utility And Military Power And Control-Circuit Applications

General

Catalog Number	TN1014
Color Code	Yellow
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	Ring Tongue
UPC	781810734209

Dimensions

Cable Insulation Diameter Maximum	0.21 in
Dimension - Bolt Size fraction	#12 - 1/4
Dimension - L Length Overall mm	34 mm
Dimension - Length Overall inch	1.32 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	11/32 in



Dimension - Stud Size inch	#12;1/4
Dimension - Z (inch)	0.37 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Pallet Quantity	99999

Product Assets

- [3D Models - TN1014_MODEL-STEP](#)
- [3D Models - TN1014_MODEL-IGES](#)
- [3D Models - TN1014_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_TN186_LineArt](#)
- [Sales Drawings - 50094155](#)
- [Specifications - TN1014](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-TN1014-SPEC-EN | REV 10/2024