

TP1010F, Vinyl Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # TP1010F



Copper Terminal, Fork Tongue, 12-10 AWG, #8-#10 Stud, Vinyl Insulated, Tin Plated.

Application

- For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Catalog Number	TP1010F
Color Code	Yellow
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	TP-F
UPC	781810710883
UPC 12 Digit	7818107108833

Dimensions

Cable Insulation Diameter Maximum	0.26 in
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Bolt Size fraction	#10
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.07 in
Dimension - Pad Width inch	0.41 in

Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#10
Dimension - Z (inch)	0.31 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Pallet Quantity	99999

Product Assets

- [3D Models - TP1010F_MODEL-PDF](#)
- [3D Models - TP1010F_MODEL-IGES](#)
- [3D Models - TP1010F_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_TP1010F_LineArt](#)
- [Sales Drawings - 50094171](#)
- [Specifications - TP1010F](#)