

## TP1012, Vinyl Ring Terminal For 12 - 10 AWG

By Burndy  
Catalog # TP1012



Ring Tongue Terminal, Polyvinylchloride, 600 VOLTS MAX. 105 Deg C MAX.

### Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serrations in the inner barrel provides added holding strength and better conductivity

### Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

### General

Catalog Number	TP1012
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810524299
UPC 12 Digit	7818105242999

### Dimensions

Cable Insulation Diameter Maximum	0.26 in
Dimension - Bolt Size fraction	1/2

Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.51 in
Dimension - Pad Width inch	0.69 in
Dimension - Strip Length inch	19/64 in
Dimension - Stud Size inch	1/2 in
Dimension - Z (inch)	0.61 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	100
-----------------	-----

### Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_TP1010\\_LineArt](#)  
[Sales Drawings - 50093722](#)  
[Specifications - TP1012](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_MX-TP1012-SPEC-EN | REV 10/2024