

## TP1014F, Vinyl Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # TP1014F



Copper Terminal, Fork Tongue, 12-10 AWG, 1/4" Stud, Vinyl Insulated, Tin Plated, Wire strip Length: 19/64"

### General

Catalog Number	TP1014F
Color Code	Yellow
Connector Type	Fork Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Trade Name	VINYLUG™
UPC	621945047105
UPC 12 Digit	6219450471055

### Dimensions

Cable Insulation Diameter Maximum	0.26 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	13/50
Dimension - Hole Size inch	0.26 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.26 in

Dimension - Pad Width inch	0.47 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	1/4 in
Dimension - Z (inch)	0.46 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	100
-----------------	-----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - TP1014F](#)