

TP106F, Vinyl Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # TP106F



Copper Terminal, Fork Tongue, 12-10 AWG, #4-#6 Stud, Vinyl Insulated, Tin Plated.

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Catalog Number	TP106F
Color Code	Yellow
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	TP-F
UPC	781810710487
UPC 12 Digit	7818107104877

Dimensions

Cable Insulation Diameter Maximum	0.26 in
Dimension - Bolt Size fraction	#6
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in

Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#6
Dimension - Z (inch)	0.26 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_TP1010F_LineArt](#)
- [Sales Drawings - 50094171](#)
- [Specifications - TP106F](#)