

TP1438, Vinyl Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # TP1438

Terminal-Polyvinylchloride Insulated, Ring Tongue, 3/8" stud, 1.15 in L, 53 in W, 600 Volts Max., 105 Deg C Max.

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serrations in the inner barrel provides added holding strength and better conductivity

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Catalog Number	TP1438
Color Code	Blue
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810085530
UPC 12 Digit	7818100855300

Dimensions

Cable Insulation Diameter Maximum	0.19 in
Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Bolt Size fraction	3/8



Dimension - Diameter Max Size inch	0.19 in
Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.40 in
Dimension - L Length Overall mm	31 mm
Dimension - Length Overall inch	1.21 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	13/64 in
Dimension - Stud Size inch	3/8 in
Dimension - Z (inch)	0.45 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#16 AWG to #14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

