

# TP148F, Vinyl Fork Terminal For 16 - 14 AWG

By Burndy  
Catalog # TP148F



Copper Terminal, Fork Tongue, 16-14 AWG, #6-#8 Stud, Vinyl Insulated, Tin Plated.

## Application

- For Commercial And Light Duty Industrial Control And Power Circuit Applications

## General

Catalog Number	TP148F
Color Code	Blue
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	TP-F
UPC	781810712689
UPC 12 Digit	7818107126899

## Dimensions

Cable Insulation Diameter Maximum	0.18 in
Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.86 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	13/64

Dimension - Stud Size inch	#6;#8
Dimension - Z (inch)	0.26 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1200
Pallet Quantity	99999

## Product Assets

- [3D Models - TP148F\\_MODEL-IGES](#)
- [3D Models - TP148F\\_MODEL-PDF](#)
- [3D Models - TP148F\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_TP1010F\\_LineArt](#)
- [Sales Drawings - 50094171](#)
- [Specifications - TP148F](#)