

## TP166F, Vinyl Fork Terminal For 22 - 16 AWG

By Burndy  
Catalog # TP166F



Copper Terminal, Fork Tongue, 22-16 AWG, #4-#6 Stud, Vinyl Insulated, Tin Plated.

### Application

- For Commercial And Light Duty Industrial Control And Power Circuit Applications

### General

Catalog Number	TP166F
Color Code	Red
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	TP-F
UPC	781810714485
UPC 12 Digit	7818107144855

### Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Bolt Size fraction	#6
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - L Length Overall mm	20 mm
Dimension - Length Overall inch	0.80 in
Dimension - Pad Width inch	0.28 in

Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#6
Dimension - Z (inch)	0.23 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor Range	#20 AWG to #22 AWG; 16 AWG to 18 AWG
Conductor Size	22 - 16 AWG
Conductor Type	<ul style="list-style-type: none"> <li>CU C Solid-Size</li> <li>CU C Str-Size</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	1200
Pallet Quantity	99999

### Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_TP1010F\\_LineArt](#)  
[Sales Drawings - 50094171](#)  
[Specifications - TP166F](#)