

Stainless Steel Nest U Die, 400 kcmil N400, Index 19

By Burndy
Catalog # U32D1



Nest U Die, 400 kcmil N400, Index 19.

Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Nest U Die
- Index 19

Application

Crimping

General

Application - For Use On	Use with Y35, Y750, PAT750; Y46 and PAT46 with PUADP1 Adapter
Catalog Number	U32D1
Crimp Force Capacity	12 ton
Die Index	19 with Y34PR; 1026 with Y34PR2
Die Type	U Die

Type	Die
UPC	781810008119
UPC 12 Digit	7818100081199

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Carton Quantity	1
Package Contents	Die only

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_UD3_LineArt](#)
- [Sales Drawings - 10035172-01](#)
- [Specifications - U32D1](#)