



Stainless Steel Circular Non-Butting Twin U Die, 750 kcmil, 600 Flex, Black, Index 24

By Burndy
Catalog # U39RT

Non-Butting U Die, 750 kcmil, 600 Flex, Black, Index 24.



Application

Crimping

General

Application - For Use On	Use with Y35, Y750, PAT750; Y46 and PAT46 with PUADP1 Adapter
Catalog Number	U39RT
Color Code	Black
Construction Material - Main	Stainless Steel
Crimp Force Capacity	12 ton
Die Index	24
Die Type	U Die
EU RoHS Indicator	Yes
Type	Die
UPC	781810627433
UPC 12 Digit	7818106274333

Dimensions

Dimension - Width inch	1.38
Dimension - Width mm	35
Weight	0.26 lb

Conductor Related

Crimping Ranges 750 Kcmil/600 Flex

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity 1
Minimum Pack Quantity 1
Package Contents Die only

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_u8crtla](#)
[Sales Drawings - 10102827](#)
[Specifications - U39RT](#)