

UC28R

By Burndy
Catalog # UC28R



Cast Aluminum Alloy TAPIT™, 1/0 (Str.) AWG-4/0 (Str.) AL, CU & ACSR (Groove A), 8 (SOL.) AWG-1/0 (Str.) AWG AL & CU (Groove B), 6 AWG-1/0 AWG ACSR (Groove B)

General

Catalog Number	UC28R
Material	Aluminum Alloy, Cast
Plated	N
Plating Type	Unplated
Trade Name	TAPIT™
UPC	781810094754
UPC 12 Digit	7818100947544

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.375 in
Dimension - Height fraction	2-3/8 in
Dimension - Height inch	2.21 in
Dimension - Height mm	56 mm
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.92 in
Dimension - Width mm	49 mm

Conductor Related

Conductor - AL Str Size A	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Size A Range	1/0 AWG-4/0 AWG
Conductor - AL Str Size B	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Size B Range	8 AWG-1/0 AWG
Conductor - Copper Solid Size B	8 AWG

Conductor - Copper Str Size A	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size A Range	1/0 AWG -4/0 AWG
Conductor - Copper Str Size B	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Str Size B Range	8 AWG-1/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_UC-RS_LineArt](#)
- [Sales Drawings - SC037822-01_A](#)
- [Specifications - UC28R](#)
- [Specifications - BURNDY_UC28R_Specsheet](#)