



UC2W28L, Cast Copper Alloy Universal Parallel Clamp

By Burndy
Catalog # [UC2W28L](#)



Cast Copper Alloy Universal Parallel Clamp, 2 Sol. - 4/0 Str, 1-1/8 Length, 1-3/4 in Width, Tin-plated.

Application

For All Combinations Of Copper, Aluminum, ACSR, 6201, 5005, Steel And Copperweld

General

Catalog Number	UC2W28L
EU RoHS Indicator	Yes
Installation Torque	110 LBS/in
Recommended in-lb Plated	N
Plating Type	Tin - Electro Plated
Sub Brand	TAPIT
Type	UC-L, Universal
UPC	781810094907

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.125 in
Dimension - Height fraction	1-1/2 in
Dimension - Height inch	1.50 in
Dimension - Width fraction	1-3/4 in
Dimension - Width inch	1.75 in

Conductor Related

Conductor - AAAC 5005 Size	77.47 (7) kcmil;123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 5005 Size Range	77.47 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Size	77.47 (7) kcmil;123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 6201 Size Range	77.47 (7) kcmil-246.9 (7) kcmil
Conductor - AL Str Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Size Range	2 AWG-4/0 AWG
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Solid Size Range	2 AWG
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size A	2 - 4/0
Conductor - Copper Str Size A Range	2 - 4/0
Conductor - Copper Str Size B	2 - 4/0
Conductor - Copper Str Size B Range	2 - 4/0
Conductor - Copper Str Size Range	2 AWG-4/0 AWG
Conductor - CopperWeld C Solid Size	8 AWG;7 AWG;6 AWG
Conductor - CopperWeld Solid Size Range	8 AWG-6 AWG
Conductor - Galvanized Steel Str Size	9/32 (7) in;5/16 (7) in;3/8 (7) in;7/16 (7) in;1/2 (19) in;9/16 (19) in
Conductor - Galvanized Steel Str Size Range	9/32 (7) in-9/16 (19) in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_UCL_lineart](#)
[Sales Drawings - SC..017162-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-UC2W28L-SPEC-EN | REV 8/2024