

Stainless Steel W Die, Index 162

By Burndy
Catalog # W162

W Die, Index 162.



Application

Crimping

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Catalog Number	W162
Construction Material - Main	Stainless Steel
Crimp Force Capacity	6 ton
Die Index	162
Die Type	W Die
EU RoHS Indicator	Yes
Type	W-Die for Hydraulic Crimping Tools (set)
UPC	781810440261
UPC 12 Digit	7818104402611

Conductor Related

Crimping Ranges

Aluminum: #4 AWG

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity	80
Package Contents	Die only
Pallet Quantity	11520

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WDIE_Lineart](#)
- [Sales Drawings - 10102381](#)
- [Specifications - W162](#)